

PROVENEER™ Flow

VENEER RESIN CEMENT

Offers ideal adhesive cementation with high mechanical properties for ceramic or composite restorations with low film thickness.

Features & Benefits

- Easy to apply with high precision due to optimally balanced flow.
- Easy to remove excess, thanks to its non-sticky consistency.
- High translucency for aesthetic results.
- Simple and direct application.
- Low film thickness ensuring a closer fit of the restoration.
- Efficient in comparison to highly flowable or pre-heated conventional composites.
- Radiopaque for useful diagnostic and excellent identification under x-ray.
- For best results use with ProLink™ Universal.
- Compatible with all bonding.
- Used in Light-cure modes.

* Available in 4 shades.



Low Film Thickness



Light Cured



Ready For Application



Radiopaque



Highly Aesthetic

Applications	Metal / PFM	Porcelain / Ceramics *	Zirconia / Alumina	Resin / Composite
Veneers	N.A	■	-	■ ■

* When used in conjunction with silane coupling agent on the restorative.



VENEERS